



Printed Machine Stretch film  
"Do not accept if seal is broken" printed



## Product Data Sheet

Effective 11/2018

### Item ID Numbers:

PRCMF2080A-DNA



DO NOT ACCEPT IF SEAL IS BROKEN

### Nominal Values: (+/-15%)

Film Properties	ASTM Test Method	80 Gauge
Tensile @ Break MD (psi)	D-882	6,250
Tensile @ Break TD (psi)	D-882	4,300
Tensile @ Yield MD (psi)	D-882	1,250
Tensile @ Yield TD (psi)	D-882	1,150
Elongation MD (%)	D-882	680
Elongation TD (%)	D-882	820
Elmendorf Tear MD (g/mil)	D-1922	500
Elmendorf Tear TD (g/mil)	D-1922	900

We believe the statements and information contained herein are accurate but are to be used only as general guidelines and are not warrants or guarantees because of the variety of possible uses. THERE IS NO WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE. THE BUYER MUST TEST THE SUITABILITY FOR EACH INTENDED APPLICATION BEFORE USING. WRAPTITE WILL NOT BE LIABLE FOR DAMAGES IN EXCESS OF THE PURCHASE PRICE OF ITS PRODUCTS OR FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES.

### Wrap Tite, Inc.

6200 Cochran Rd.

Solon, Ohio 44139

**Toll Free:** 888-WRAP TITE (972-7848)

**Fax:** 440-349-5432

[www.wraptite.com](http://www.wraptite.com) – [info@wraptite.com](mailto:info@wraptite.com)



MD = Machine Direction

TD = Transverse Direction